



HMC499T

## MCB 4P 15kA C-125A 6M

### Technical properties

#### Architecture

Type of pole	4P
Curve	C

#### Voltage

Rated operational voltage $U_e$	415 - 415 V
Type voltage supply	AC
Rated insulation voltage $U_i$	500 V
Rated impulse withstand voltage $U_{imp}$	6000 V

#### Frequency

Frequency	50 - 60 Hz
-----------	------------

#### Installation, mounting

Nominal tightening torque	3,5 - 5,0 Nm
Type of top connection for modular devices	Screw terminal
Type of bottom connection for modular devices	Screw terminal

#### Electric current

Rated current	125 A
Rated short-circuit breaking capacity $I_{cn}$ under 230 V AC according to IEC 60898-1	15 kA
Rated ultimate short-circuit breaking capacity $I_{cu}$ under 230 V AC IEC 60947-2	15 kA
Rated ultimate short-circuit breaking capacity $I_{cu}$ under 400 V AC IEC 60947-2	15 kA
Rated current 30°C	125 A
Rated current 35°C	122 A
Rated current at 40°C	119 A
Rated current at 45°C	115,70 A
Rated current at 50°C	112 A
Rated current 55°C	109,10 A
Rated current 60°C	105,60 A

#### Main electrical attributes

Rated short-circuit breaking capacity $I_{cn}$ AC according to IEC 60898-1	15 kA
Nominal tightening torque down terminal	3,60 - 3,60 Nm
Nominal tightening torque top terminal	3,60 - 3,60 Nm

#### Power

**Endurance**

Electric endurance in number of cycles	4000
Number of mechanical operations	20000

**Connection**

Cross-section of input and output with screws, for massive conductors	1 - 70 mm <sup>2</sup>
Cross-section of input and output with screws, for flexible conductors	1 - 50 mm <sup>2</sup>

**Use conditions**

Degree of pollution according to IEC 60664 / IEC 60947-2	3
Air humidity protection	For all climates

**Capacity**

Number of modules	6
-------------------	---

**Connectivity**

Top connection alignment for modular devices	Aligned terminal
Down connection alignment for modular devices	Aligned terminal

**Dimensions**

Height	90 mm
Width	106 mm
Depth	70 mm