



HIB463M

### Motorized transfer switch 4P 630A

#### Technical properties

##### Voltage

Rated operational voltage  $U_e$  380 - 415 V

##### Electric current

Rated current 630 A

Rated conditional short-circuit current  $I_{cc}$   
with gI-gG fuses 50 kA

##### Power

Rated operational power under 400 V AC  
AC1 414000 W

##### Architecture

Number of poles 4

Device construction type Fixed built-in

##### Compatibility

Suitable for DIN Rail Yes

Suitable for distribution board Yes