



HNB200U

Moulded Case Circuit Breaker X250 3P 40kA 200A TM

Technical properties

Electric current

Rated current	200 A
Rated ultimate short-circuit breaking capacity Icu under 400 V AC IEC 60947-2	40 kA
Rated ultimate short-circuit breaking capacity Icu under 240 V AC IEC 60947-2	85 kA
Rated current 10°C according to IEC 60947	238,60 A
Rated current 15°C according to IEC 60947	234,20 A
Rated current 20°C according to IEC 60947	229,80 A
Rated current 25°C according to IEC 60947	225 A
Rated current 30°C according to IEC 60947	220,20 A
Rated current at 35°C according to IEC 60947	215,40 A
Rated current at 40°C according to IEC 60947	210,40 A
Rated current 45°C according to IEC 60947	205,20 A
Rated current 50°C according to IEC 60947	200 A
Rated current 55°C according to IEC 60947	194,60 A
Rated current at 60°C according to IEC 60947	189 A
Rated current 65°C according to IEC 60947	183,40 A
Rated current 70°C according to IEC 60947	177,80 A

Architecture

Number of poles	3
Control/operation element	Toggle
Device construction type	Fixed built-in

Tripping

Response time when opening	10 ms
----------------------------	-------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Voltage

Rated impulse withstand voltage Uimp	8000 V
Rated insulation voltage Ui	800 V
Rated operational voltage Ue	220 - 415 V

Functions

Trip unit	TM A/A
-----------	--------

Power	
Total power loss under IN	24,80 W
Endurance	
Electric endurance in number of cycles	1000
Number of mechanical operations	4000
Safety	
Ingress Protection (IP) class	IP4X
Connection	
Cross-section flexible conductor	35 - 150 mm ²
Cross-section rigid conductor	35 - 185 mm ²
Settings	
Thermal protection knob setting xIN	0.63, 0.8, 1
Adjustment range short-term delayed short-circuit release	0 - 0 A
Compatibility	
Suitable for DIN Rail	No
Installation, mounting	
Mounting-/Connection Position	Front
Nominal tightening torque	12 - 12 Nm
Main electrical attributes	
Magnetic protection trip time	0 - 0 ms