



**Insulated busbar 1P 63A prong 10mm<sup>2</sup> blue 18M**

**Technical properties**

**Architecture**

|                 |     |
|-----------------|-----|
| Number of poles | 1 P |
| Type of pole    | 1 P |

**Configuration**

|                   |    |
|-------------------|----|
| Number of modules | 13 |
|-------------------|----|

**Compatibility**

|  |                 |
|--|-----------------|
| Intended for the compatible references | Modular devices |
|--|-----------------|

**Main electrical features**

|                              |       |
|------------------------------|-------|
| Rated operational voltage Ue | 415 V |
|------------------------------|-------|

**Voltage**

|                                 |       |
|---------------------------------|-------|
| Max operating voltage           | 230 V |
| Rated impulse withstand voltage | 4 kV  |

**Electric current**

|               |      |
|---------------|------|
| Rated current | 63 A |
|---------------|------|

**Dimensions**

|                                   |         |
|-----------------------------------|---------|
| Length                            | 228 mm  |
| Pitch                             | 17.8 mm |
| Fixation distance in module steps | 1       |

**Power supply**

|                                       |         |
|---------------------------------------|---------|
| Number of phases for the power supply | 1 phase |
|---------------------------------------|---------|

**Installation, mounting**

|  |    |
|--|----|
| Suitable to a device with an auxiliary | No |
|--|----|

**Connection**

|  |                   |
|--|-------------------|
| Connection cross-sect. rigid cable       | 10mm <sup>2</sup> |
| Suitable for product with neutral busbar | No                |
| Connector type                           | busbar prong      |
| Type of connection                       | with screw        |

**Equipment**

|                                  |    |
|----------------------------------|----|
| Number of appliances to build in | 13 |
|----------------------------------|----|

**Safety**

|               |     |
|---------------|-----|
| REACH conform | Yes |
|---------------|-----|

KB163NG

RoHS conform

Yes

**Use conditions**

---

Insulated

Yes