



KRN163

Neutral connecting block 63A

Technical properties

Architecture

Number of poles	1 P
Type of pole	N

Functions

Suitable for fine strand conductors	No
Suitable for fine strand conductors without cable end sleeve	No
Suitable for extra fine-strand conductors	No
Suitable for extra fine-strand conductors without cable end sleeve	No

Configuration

Number of modules	1
-------------------	---

Main electrical features

Rated operational voltage Ue	230 / 400 V
Type of supply voltage	AC

Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	4 kV

Electric current

Rated current	63 A
---------------	------

Dimensions

Depth of installed product	60 mm
Height of installed product	83.5 mm
Width of installed product	17.5 mm

Frequency

Frequency	50 to 60 Hz
-----------	-------------

Installation, mounting

Tightening torque	2,8Nm
-------------------	-------

Connection

Connection cross-section of input and output with screws, for massive conductors	1 / 35 mm ²
Connection cross section of access and exit with screws, for flexible conductor	2.5 / 25 mm ²

Equipment

Number of outputs	1
Number of inputs	1

Safety

REACH conform	Yes
RoHS conform	Yes

Use conditions

Operating temperature	-25...60 °C
Altitude	2000 m
Storage/transport temperature	-25...80 °C
