



HNC126H

**Moulded Case Circuit Breaker h250 4P 50kA 125A LSI**

**Technical properties**

**Electric current**

Rated current	125 A
Rated ultimate short-circuit breaking capacity Icu under 400 V AC IEC 60947-2	50 kA
Rated ultimate short-circuit breaking capacity Icu under 240 V AC IEC 60947-2	85 kA

**Architecture**

Number of poles	4
-----------------	---

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Voltage**

Rated impulse withstand voltage Uimp	8000 V
Rated insulation voltage Ui	800 V

**Functions**

Trip unit	LSI
-----------	-----

**Main electrical attributes**

Magnetic protection trip time	100 - 200 ms
-------------------------------	--------------

**Power**

Total power loss under IN	18,30 W
---------------------------	---------

**Endurance**

Electric endurance in number of cycles	1000
Number of mechanical operations	4000

**Safety**

Ingress Protection (IP) class	IP4X
-------------------------------	------

**Use conditions**

Operating temperature	-25 - 70 °C
-----------------------	-------------

**Connection**

Cross-section flexible conductor	35 - 150 mm <sup>2</sup>
Cross-section rigid conductor	35 - 185 mm <sup>2</sup>
Connector/plug type	Terminal

**Installation, mounting**

Nominal tightening torque	12 - 12 Nm
---------------------------	------------

Mounting-/Connection Position	Front
<b>Settings</b>	
Thermal protection knob setting xIN	0.4, 0.5, 0.63, 0.8, 0.9, 0.95, 1
Adjustment range short-term delayed short-circuit release	0 - 0 A