



HTG911H

**Power supply 24V DC 2,5A at 70°C**

**Technical properties**

**Configuration**

Number of modules	4
-------------------	---

**Main electrical features**

Rated operational voltage Ue	196 / 264 V
Type of supply voltage	AC

**Voltage**

Output voltage	24 V DC
Rated operational voltage in DC	0 V

**Electric current**

Output intensity	2.5 A
Output intensity	2.5 A

**Dimensions**

Depth of installed product	63 mm
Height of installed product	93 mm
Installation height	0 m
Width of installed product	71 mm

**Frequency**

Frequency	50 to 60 Hz
-----------	-------------

**Power**

Power absorbed	60 W
Total power loss under IN	6 W

**Installation, mounting**

Suitable for busbar mounting	No
Suitable for front mounting	No

**Connection**

Connection cross-section of input and output with screws, for massive conductors	1 / 2.5 mm <sup>2</sup>
Connection cross section of access and exit with screws, for flexible conductor	0.75 / 2.5 mm <sup>2</sup>
Type of connection	Screw connection

**Equipment**

Short-circuit protected	Yes
-------------------------	-----

**Standards**

---

European directive RoHs	compliant
-------------------------	-----------

**Use conditions**

---

Operating temperature	-25...70 °C
-----------------------	-------------

---

Storage/transport temperature	-40...85 °C
-------------------------------	-------------