



MDN263P

## MCB 2P 6kA D-63A 2M

### Technical properties

#### Electric current

Rated current	63 A
Rated current -15°C	78,07 A
Rated current -10°C	76,54 A
Rated current -5°C	75,05 A
Rated current at 0°C	73,54 A
Rated current 5°C	72,03 A
Rated current 10°C	70,52 A
Rated current 15°C	69 A
Rated current at 20°C	67,47 A
Rated current 25°C	65,95 A
Rated current 30°C	63 A
Rated current 35°C	62,03 A
Rated current at 40°C	60,50 A
Rated current at 45°C	58,68 A
Rated current at 50°C	58,27 A
Rated current 55°C	52,80 A
Rated current 60°C	50,51 A
Rated current 65°C	48,12 A
Rated current 70°C	45,60 A

#### Architecture

Type of pole	2P
Curve	D

#### Capacity

Number of modules	2
-------------------	---

#### Main electrical attributes

Rated short-circuit breaking capacity I <sub>cn</sub> AC according to IEC 60898-1	6 kA
Nominal tightening torque top terminal	2,80-2,80 Nm
Nominal tightening torque down terminal	2,80-2,80 Nm

#### Voltage

Rated operational voltage U <sub>e</sub>	415-415 V
Type voltage supply	AC
Rated insulation voltage U <sub>i</sub>	500 V
Rated impulse withstand voltage U <sub>imp</sub>	6000 V

<b>Frequency</b>	
Frequency	50-60 Hz
<b>Connection</b>	
Cross-section of input and output with screws, for massive conductors	1-35 mm <sup>2</sup>
Cross-section of input and output with screws, for flexible conductors	1-25 mm <sup>2</sup>
Cross-section of input with screws, for flexible conductors	1-25 mm <sup>2</sup>
Cross-section of input with screws, for massive conductors	1-35 mm <sup>2</sup>
<b>Installation, mounting</b>	
Nominal tightening torque	2,80-2,80 Nm
Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal
360° mounting position possible	Yes
<b>Safety</b>	
Ingress Protection (IP) class	IP20
<b>Use conditions</b>	
Degree of pollution according to IEC 60664 / IEC 60947-2	2
Air humidity protection	95%/55°C
Operating temperature	-25-70 °C
<b>Power</b>	
Total power loss under IN	13,10 W
<b>Connectivity</b>	
Type of connection	Screw terminal
Top connection alignment for modular devices	Aligned terminal
Down connection alignment for modular devices	Aligned terminal
<b>Dimensions</b>	
Height	84,60 mm
Width	35 mm
Depth	70 mm