



HTG911H

**Power supply 24V DC 2,5A at 70°C**

**Technical properties**

**Configuration**

Number of modules 4

**Main electrical features**

Rated operational voltage Ue 196 / 264 V

Type of supply voltage AC

**Voltage**

Output voltage 24 V DC

Rated operational voltage in DC 0 V

**Electric current**

Output intensity 2.5 A

Output intensity 2.5 A

**Dimensions**

Depth of installed product 63 mm

Height of installed product 93 mm

Installation height 0 m

Width of installed product 71 mm

**Frequency**

Frequency 50 to 60 Hz

**Power**

Power absorbed 60 W

Total power loss under IN 6 W

**Installation, mounting**

Suitable for busbar mounting No

Suitable for front mounting No

**Connection**

Connection cross-section of input and output with screws, for massive conductors 1 / 2.5 mm<sup>2</sup>

Connection cross section of access and exit with screws, for flexible conductor 0.75 / 2.5 mm<sup>2</sup>

Type of connection Screw connection

**Equipment**

Short-circuit protected Yes

**Standards**

---

European directive RoHS	compliant
European directive WEEE	concerned

---

**Safety**

---

Protection index IP	IP20
---------------------	------

---

**Use conditions**

---

Operating temperature	-25...70 °C
Storage/transport temperature	-40...85 °C

---