



MSN106

**MCB 1P 6kA C-6A 1M**

**Technical properties**

**Electric current**

Rated current	6 A
Rated short-circuit breaking capacity I <sub>cn</sub> under 230 V AC according to IEC 60898-1	6 kA
Rated current -15°C	7,5 A
Rated current -10°C	7,4 A
Rated current -5°C	7,2 A
Rated current at 0°C	7,1 A
Rated current 5°C	6,9 A
Rated current 10°C	6,7 A
Rated current 15°C	6,6 A
Rated current at 20°C	6,4 A
Rated current 25°C	6,2 A
Rated current 30°C	6 A
Rated current 35°C	5,8 A
Rated current at 40°C	5,6 A
Rated current at 45°C	5,4 A
Rated current at 50°C	5,2 A
Rated current 55°C	5 A
Rated current 60°C	4,7 A
Rated current 65°C	4,5 A
Rated current 70°C	4,2 A

**Architecture**

Type of pole	1P
Curve	C

**Capacity**

Number of modules	1
-------------------	---

**Main electrical attributes**

Rated short-circuit breaking capacity I <sub>cn</sub> AC according to IEC 60898-1	6 kA
Nominal tightening torque top terminal	2,80 - 2,80 Nm
Nominal tightening torque down terminal	2,80 - 2,80 Nm

**Voltage**

Rated operational voltage U <sub>e</sub>	240 - 415 V
Type voltage supply	AC
Rated insulation voltage U <sub>i</sub>	500 V

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Connection**

Cross-section of input and output with screws, for massive conductors	1 - 35 mm <sup>2</sup>
Cross-section of input and output with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for massive conductors	1 - 35 mm <sup>2</sup>

**Installation, mounting**

Nominal tightening torque	2,80 - 2,80 Nm
Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal
360° mounting position possible	Yes

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Use conditions**

Degree of pollution according to IEC 60664 / IEC 60947-2	2
Class of energy limitation I <sup>2</sup> t	3
Air humidity protection	For all climates
Operating temperature	-25 - 70 °C

**Power**

Total power loss under IN	1,3 W
---------------------------	-------

**Connectivity**

Type of connection	Screw terminal
Top connection alignment for modular devices	Aligned terminal
Down connection alignment for modular devices	Aligned terminal

**Dimensions**

Height	83 mm
Width	17,50 mm
Depth	70 mm