



MSN132R

**MCB 1P 6kA C-32A 1M**

**Technical properties**

**Electric current**

Rated current	32 A
Rated short-circuit breaking capacity I <sub>cn</sub> under 230 V AC according to IEC 60898-1	6 kA
Rated current -15°C	40,2 A
Rated current -10°C	39,6 A
Rated current -5°C	38,5 A
Rated current at 0°C	37,7 A
Rated current 5°C	36,9 A
Rated current 10°C	36,1 A
Rated current 15°C	35,2 A
Rated current at 20°C	34,4 A
Rated current 25°C	33,6 A
Rated current 30°C	32 A
Rated current 35°C	32 A
Rated current at 40°C	31,1 A
Rated current at 45°C	30,3 A
Rated current at 50°C	30 A
Rated current 55°C	28,7 A
Rated current 60°C	27,8 A
Rated current 65°C	27 A
Rated current 70°C	26,2 A

**Architecture**

Type of pole	1P
Curve	C

**Capacity**

Number of modules	1
-------------------	---

**Main electrical attributes**

Rated short-circuit breaking capacity I <sub>cn</sub> AC according to IEC 60898-1	6 kA
Nominal tightening torque top terminal	2,80 - 2,80 Nm
Nominal tightening torque down terminal	2,80 - 2,80 Nm

**Voltage**

Rated operational voltage U <sub>e</sub>	240 - 415 V
Type voltage supply	AC
Rated insulation voltage U <sub>i</sub>	500 V

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Connection**

Cross-section of input and output with screws, for massive conductors	1 - 35 mm <sup>2</sup>
Cross-section of input and output with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for massive conductors	1 - 35 mm <sup>2</sup>

**Installation, mounting**

Nominal tightening torque	2,80 - 2,80 Nm
Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal
360° mounting position possible	Yes

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Use conditions**

Degree of pollution according to IEC 60664 / IEC 60947-2	2
Class of energy limitation I <sup>2</sup> t	3
Air humidity protection	For all climates
Operating temperature	-25 - 70 °C

**Power**

Total power loss under IN	4,35 W
---------------------------	--------

**Connectivity**

Type of connection	Screw terminal
Top connection alignment for modular devices	Aligned terminal
Down connection alignment for modular devices	Aligned terminal

**Dimensions**

Height	83 mm
Width	17,50 mm
Depth	70 mm