



KCL363L

Busbar MCB 3P 2R 125mm left

Technical properties

Architecture

| | |
|-----------------|-----|
| Number of poles | 3 P |
| Type of pole | 3 P |

Compatibility

| | |
|--|-------------------------------|
| Intended for the compatible references | Modular vertical distribution |
|--|-------------------------------|

Main electrical features

| | |
|------------------------------|-------------|
| Rated operational voltage Ue | 110 / 415 V |
|------------------------------|-------------|

Voltage

| | |
|---------------------------------|-------|
| Max operating voltage | 456 V |
| Rated impulse withstand voltage | 4 kV |

Electric current

| | |
|---------------|------|
| Rated current | 63 A |
|---------------|------|

Dimensions

| | |
|--------|---------|
| Length | 146 mm |
| Pitch | 17.8 mm |

Power supply

| | |
|---------------------------------------|---------|
| Number of phases for the power supply | 3-phase |
|---------------------------------------|---------|

Materials

| | |
|--------|------------|
| Colour | stone grey |
|--------|------------|

Installation, mounting

| | |
|--|-------------------------|
| Mounting way | vertical left hand side |
| Suitable to a device with an auxiliary | No |

Connection

| | |
|--|----|
| Suitable for product with neutral busbar | No |
|--|----|

Cable

| | |
|----------------|--------------------|
| Conductor Size | 10 mm ² |
|----------------|--------------------|

Standards

| | |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

Use conditions

| | |
|-----------|-----|
| Insulated | Yes |
|-----------|-----|