




MZ202



## Alarm contact 1C+1O 6A 240V AC

### Technical properties

#### Configuration

Number of modules	0.5
-------------------	-----

#### Main electrical features

Rated operational voltage U <sub>e</sub>	230 / 415 V
Type of supply voltage	AC

#### Voltage

Rated insulation voltage	4000 V
Max operating voltage	240 V
Rated operational voltage in DC	12 / 250 V

#### Electric current

Acceptable current rating with AC1	6 A
Rated current	6 A
I <sub>min</sub> =f(U=12V DC) for power circuit	0.3 A
I <sub>min</sub> = f (U = 230 V DC)	0.6 A
I <sub>min</sub> =f(U=400V AC) for power circuit	3 A

#### Dimensions

Depth of installed product	68 mm
Width of installed product	9 mm

#### Power

Total power loss under I <sub>N</sub>	0.2 W
---------------------------------------	-------

#### Endurance

Electric endurance in number of cycles	6000
Number of mechanical operations	12000

#### Installation, mounting

Tightening torque	1,3Nm
Factory fitted	No

#### Connection

Connection cross-sect. flexible conductor	6mm <sup>2</sup>
Connection cross-sect. rigid cable	10mm <sup>2</sup>
Type of contacts	1NC+1NO

#### Equipment

Quantity of NC contacts	1
-------------------------	---

Quantity of NO contacts	1
Quantity of INV contacts	0
<b>Standards</b>	
European directive WEEE	concerned
<b>Safety</b>	
Halogen free	No
<b>Use conditions</b>	
Operating temperature	-25...60 °C
Air humidity protection	95% / 80°C
Storage/transport temperature	-40...80 °C