



KRN163

**Neutral connecting block 63A**

**Technical properties**

**Architecture**

Number of poles	1 P
Type of pole	N
Fixing mode	DIN rail type O (symmetrical)

**Functions**

Suitable for fine strand conductors	No
Suitable for fine strand conductors without cable end sleeve	No
Suitable for extra fine-strand conductors	No
Suitable for extra fine-strand conductors without cable end sleeve	No

**Configuration**

Number of modules	1
-------------------	---

**Main electrical features**

Rated operational voltage Ue	230 / 400 V
Type of supply voltage	AC

**Voltage**

Rated insulation voltage	500 V
Rated impulse withstand voltage	4 kV

**Electric current**

Rated current	63 A
---------------	------

**Dimensions**

Depth of installed product	60 mm
Height of installed product	83.5 mm
Width of installed product	17.5 mm

**Frequency**

Frequency	50 to 60 Hz
-----------	-------------

**Installation, mounting**

Tightening torque	2,8Nm
-------------------	-------

**Connection**

Connection cross-section of input and output with screws, for massive conductors	1 / 35 mm <sup>2</sup>
Connection cross section of access and exit with screws, for flexible conductor	2.5 / 25 mm <sup>2</sup>

**Equipment**

Number of outputs	1
Number of inputs	1

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Safety**

Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes

**Use conditions**

Operating temperature	-25...60 °C
Altitude	2000 m
Storage/transport temperature	-25...80 °C