



SBR490

4-pole, 100A Modular Switch with Red Toggle

Technical properties

Architecture

Type of order	Break switch
Neutral position	without neutral
Number of poles	4 P

Configuration

Number of modules	4
-------------------	---

Main electrical features

Rated operational voltage Ue	400 V
------------------------------	-------

Voltage

Rated insulation voltage	440 V
Type of voltage input 1	AC
Rated impulse withstand voltage	6000 V

Electric current

Rated operational current in AC21category B	100 A
Acceptable current rating with AC22 category A	100 A
Rated current	100 A
Rated short-time withstand current 1s	1.2 kA
Thermal rated current outside of housings	100 A
Rated operational current in AC21 category A	100 A
Acceptable current rating with AC22 category B	100 A

Dimensions

Depth of installed product	69 mm
Height of installed product	83 mm
Width of installed product	70 mm

Frequency

Frequency	50 to 60 Hz
-----------	-------------

Power

Total power loss under IN	22 W
Power loss per pole at In	5.5 W

Endurance

Electrical durability at nominal load in AC21 in operating cycles	2500
Electrical durability at nominal load in AC22 in operating cycles	2500
Number of mechanical operations	40000
Installation, mounting	
Tightening torque	3,6Nm
Connection	
Connection cross-sect. flexible conductor	6 / 35mm ²
Connection cross-sect. rigid cable	6 / 50mm ²
Cage clamp position	in line
Equipment	
Quantity of NC contacts	0
Quantity of NO contacts	4
Quantity of INV contacts	0
Standards	
Standard text	IEC 60947-3
European directive WEEE	not concerned
Safety	
RoHS conform	Yes
Halogen free	No
Use conditions	
Operating temperature	-20...50 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	2
Altitude	2000 m
Storage/transport temperature	-40...80 °C