



SF463

4 pole Changeover switch 63A I-0-II

Technical properties

Architecture

Number of poles	4
Type of pole	4P

Electric current

Rated current	63 A
Rated conditional short-circuit current I _{cc} with gI-gG fuses	6 kA

Installation, mounting

Nominal tightening torque	2,90 - 2,90 Nm
---------------------------	----------------

Voltage

Rated operational voltage U _e	400 - 400 V
Type voltage supply	AC
Rated insulation voltage U _i	500 V
Rated impulse withstand voltage U _{imp}	4000 V

Capacity

Number of modules	8
-------------------	---

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Dimensions

Height	90 mm
Width	143 mm
Depth	72 mm

Equipment

Number of NO contacts	0
Number of NC contacts	0

Use conditions

Operating temperature	-25 - 50 °C
Storage/transport temperature	-40 - 80 °C

Connection

Cross-section flexible conductor	16 mm ²
----------------------------------	--------------------

Cross-section rigid conductor

25 mm²

Endurance

Number of mechanical operations	100000
---------------------------------	--------

Electrical durability at nominal load in AC21 in operating cycles	5000
--	------

Power

Total power loss under IN	7,20 W
---------------------------	--------