



SPA212A

SPD 2P monobloc 12.5kA class 1 with light indicator TT

Technical properties

Capacity

Number of modules	4
-------------------	---

Voltage

Rated operational voltage U_e	230 - 230 V
---------------------------------	-------------

Continuous operating voltage U_c according to IEC 61643-1	255 V
---	-------

Voltage protection level U_p according to IEC 61643-1	2,50 kV
---	---------

Electric current

Nominal discharge current I_n 8 - 20 μ s L-N(PEN)/N-PE IEC 61643	12.5 kA
--	---------

Max. overcurrent protection device, parallel connection (fuse)	315 A
--	-------

Max. discharge (I_{max}) L-N(PEN)/ N-PE	50 kA
---	-------

Dimensions

Height	90 mm
--------	-------

Width	72 mm
-------	-------

Depth	68 mm
-------	-------

Use conditions

Operating temperature	-40 - 60 °C
-----------------------	-------------

Network configuration

Network type	TN, TT
--------------	--------

Equipment

With remote signalling contact	No
--------------------------------	----

Standards

Requirement class IEC 61643	T1
-----------------------------	----

Frequency

Frequency	50 - 60 Hz
-----------	------------

Installation, mounting

Nominal tightening torque	3,60 - 3,60 Nm
---------------------------	----------------