



SPB040N

**Cartridge N-PE Uc 260V In 20kA I<sub>max</sub> 40kA Up 1.5kV**

**Technical properties**

**Capacity**

Number of modules	1
-------------------	---

**Voltage**

Rated operational voltage U <sub>e</sub>	240 - 415 V
--	-------------

Continuous operating voltage U <sub>c</sub> according to IEC 61643-1	260 V
--	-------

Voltage protection level U <sub>p</sub> L-PE/N-PE according to IEC 61643-11	1,5 kV
---	--------

**Electric current**

Nominal discharge current I <sub>n</sub> 8 - 20 μs L-N(PEN)/N-PE IEC 61643	20 kA
--	-------

Max. discharge (I <sub>max</sub> ) L-N(PEN)/ N-PE	40 kA
---	-------

**Dimensions**

Height	52,4 mm
--------	---------

Width	17,5 mm
-------	---------

Depth	55,3 mm
-------	---------

**Use conditions**

Operating temperature	-40 - 80 °C
-----------------------	-------------

**Network configuration**

Network type	TN, TT
--------------	--------

**Connection**

Cross-section of input and output with screws, for flexible conductors	1,5 - 25,0 mm <sup>2</sup>
--	----------------------------

Cross-section of input and output with screws, for massive conductors	1,5 - 35,0 mm <sup>2</sup>
---	----------------------------

**Standards**

Requirement class IEC 61643	T2
-----------------------------	----

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Installation, mounting**

Nominal tightening torque	3 - 3 Nm
---------------------------	----------