



SPB065N

Cartridge N-PE Uc 260V In 20kA I_{max} 65kA Up 1,5kV

Technical properties

Capacity

Number of modules	1
-------------------	---

Voltage

Rated operational voltage U _e	240 - 415 V
--	-------------

Continuous operating voltage U _c according to IEC 61643-1	264 V
--	-------

Voltage protection level U _p L-PE/N-PE according to IEC 61643-11	1,7 kV
---	--------

Electric current

Nominal discharge current I _n 8 - 20 μs L-N(PEN)/N-PE IEC 61643	50 kA
--	-------

Dimensions

Height	47,3 mm
--------	---------

Width	17,5 mm
-------	---------

Depth	67,3 mm
-------	---------

Use conditions

Operating temperature	-40 - 80 °C
-----------------------	-------------

Network configuration

Network type	TN-S, TT
--------------	----------

Connection

Cross-section of input and output with screws, for flexible conductors	1,5 - 25,0 mm ²
--	----------------------------

Cross-section of input and output with screws, for massive conductors	1,5 - 35,0 mm ²
---	----------------------------

Standards

Requirement class IEC 61643	T1, T2
-----------------------------	--------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Installation, mounting

Nominal tightening torque	3 - 3 Nm
---------------------------	----------