



SPB265R

Surge Protection Device 2P T2 TNS/TT Uc 320V In 20kA I_{max} 65kA remote contact

Technical properties

Configuration

Number of modules	2
-------------------	---

Controls and indicators

Indicator lamp	Optic
----------------	-------

Main electrical features

Rated operational voltage U _e	240 / 415 V
--	-------------

Nominal discharge current (I _n) 8/20μs, IEC 61643)L-N(PEN)/ N-PE	20 kA
--	-------

Voltage

Maximum continuous operating voltage U _c	320 V
---	-------

Voltage protection level U _p according to IEC61643-1	1.45 kV
---	---------

Voltage protection level U _p L-PE/N-PE according to IEC61643-11	1.7 kV
--	--------

Voltage level U _p L-N/PEN IEC61643-11	1.45 kV
--	---------

Electric current

Calibration of the protection upstream	160 A
--	-------

Max discharge (I _{max}) L-N(PEN)/ N-PE	65 kA
--	-------

Dimensions

Depth of installed product	58.2 mm
----------------------------	---------

Height of installed product	89.8 mm
-----------------------------	---------

Width of installed product	35.6 mm
----------------------------	---------

Electrical specifications

Short-circuit breaking capacity (I _{sc} cr)	25 kA
--	-------

Signal contact Cross-sections	0.14 / 1.5 mm ²
-------------------------------	----------------------------

Signal contact Current carrying capacity AC/DC	3 / 1 A
--	---------

Signal contact Voltage rating AC/DC	250 / 30 V
-------------------------------------	------------

Network configuration

Network type	TT/TN-S
--------------	---------

Installation, mounting

Tightening torque	3
-------------------	---

Connection

Connection cross-section of input and output with screws, for massive conductors	1.5 / 35 mm ²
Connection cross section of access and exit with screws, for flexible conductor	1.5 / 25 mm ²
Standards	
Test class IEC61643-11 / VDE0675-6-11	T2
European directive WEEE	concerned
Safety	
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Use conditions	
Operating temperature	-40...80 °C