



SK600



## Selector switch non spring ret

### Technical properties

#### Architecture

Number of poles	1
Type of pole	1P

#### Electric current

Rated current	20 A
Rated conditional short-circuit current I <sub>cc</sub> with gl-gG fuses	8 kA

#### Voltage

Rated operational voltage U <sub>e</sub>	660 - 660 V
Type voltage supply	AC
Rated insulation voltage U <sub>i</sub>	690 V

#### Capacity

Number of modules	3
-------------------	---

#### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

#### Frequency

Frequency	50 - 50 Hz
-----------	------------

#### Dimensions

Height	85 mm
Width	53 mm
Depth	64 mm

#### Equipment

Number of NO contacts	0
Number of NC contacts	0

#### Use conditions

Operating temperature	-10 - 40 °C
Storage/transport temperature	-40 - 80 °C

#### Connection

Cross-section flexible conductor	1.5 - 10 mm <sup>2</sup>
Cross-section rigid conductor	1 - 6 mm <sup>2</sup>

#### Power

Total power loss under IN	0,70 W
---------------------------	--------