



SPN408D

SPD 4P pluggable 8kA class 2 with indicator

Technical properties

Configuration

Number of modules	4
-------------------	---

Main electrical features

Rated operational voltage Ue	230 / 400 V
------------------------------	-------------

Nominal discharge current (In) 8/20μs, IEC 61643) L-N(PEN)/ N-PE	2 kA
--	------

Voltage

Maximum continuous operating voltage Uc	255 V
---	-------

Voltage protection level Up according to IEC61643-1	1.5 kV
---	--------

Voltage protection level Up L-PE/N-PE according to IEC61643-11	1.5 kV
--	--------

Voltage level Up L-N/PEN IEC61643-11	1 kV
--------------------------------------	------

Electric current

Max discharge (Imax) L-N(PEN)/ N-PE	8 kA
-------------------------------------	------

Dimensions

Width of installed product	72 mm
----------------------------	-------

Power

Total power loss under IN	0.1 W
---------------------------	-------

Standards

European directive WEEE	concerned
-------------------------	-----------

Use conditions

Operating temperature	-40...80 °C
-----------------------	-------------

Storage/transport temperature	-40...80 °C
-------------------------------	-------------