



SPN408S

SPD 4P monobloc 8kA class 2 with light indicator

Technical properties

Configuration

| | |
|-------------------|---|
| Number of modules | 3 |
|-------------------|---|

Main electrical features

| | |
|--|-------------|
| Rated operational voltage U_e | 230 / 400 V |
| Frequency | 50/60 Hz |
| Nominal discharge current (I_n) 8/20 μ s, IEC 61643)L-N(PEN)/ N-PE | 2 kA |

Voltage

| | |
|--|-------|
| Maximum continuous operating voltage U_c | 255 V |
| Voltage protection level U_p according to IEC61643-1 | 1 kV |

Electric current

| | |
|--|------|
| Max discharge (I_{max}) L-N(PEN)/ N-PE | 8 kA |
|--|------|

Dimensions

| | |
|----------------------------|-------|
| Width of installed product | 54 mm |
|----------------------------|-------|

Power

| | |
|------------------------------|-----|
| Total power loss under I_N | 0 W |
|------------------------------|-----|

Standards

| | |
|---------------------------------------|---------------|
| Test class IEC61643-11 / VDE0675-6-11 | T2 |
| European directive WEEE | not concerned |

Use conditions

| | |
|-------------------------------|-------------|
| Operating temperature | -40...60 °C |
| Storage/transport temperature | -40...80 °C |