



SPB010R

Cartridge L-N Uc 320V In 40kA I_{max} 100kA U_p 2kV

Technical properties

Configuration

| | |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

Controls and indicators

| | |
|----------------|-------|
| Indicator lamp | Optic |
|----------------|-------|

Main electrical features

| | |
|--|-------------|
| Rated operational voltage U _e | 240 / 415 V |
|--|-------------|

Voltage

| | |
|---|-------|
| Maximum continuous operating voltage U _c | 320 V |
|---|-------|

Dimensions

| | |
|----------------------------|---------|
| Depth of installed product | 58.2 mm |
|----------------------------|---------|

| | |
|-----------------------------|---------|
| Height of installed product | 89.8 mm |
|-----------------------------|---------|

Electrical specifications

| | |
|--|-------|
| Short-circuit breaking capacity (I _{sc} cr) | 25 kA |
|--|-------|

Installation, mounting

| | |
|-------------------|---|
| Tightening torque | 3 |
|-------------------|---|

Connection

| | |
|--|--------------------------|
| Connection cross-section of input and output with screws, for massive conductors | 1.5 / 35 mm ² |
|--|--------------------------|

| | |
|---|--------------------------|
| Connection cross section of access and exit with screws, for flexible conductor | 1.5 / 25 mm ² |
|---|--------------------------|

Standards

| | |
|---------------------------------------|----|
| Test class IEC61643-11 / VDE0675-6-11 | T2 |
|---------------------------------------|----|

| | |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

Safety

| | |
|---------------|-----|
| REACH conform | Yes |
|---------------|-----|

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|

| | |
|--------------|-----|
| Halogen free | Yes |
|--------------|-----|

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -40...80 °C |
|-----------------------|-------------|