



SPB240R

Surge Protection Device 2P T2 TNS/TT U_c 275V I_n 20kA I_{max} 40kA remote contact

Technical properties

Capacity

Number of modules	2
-------------------	---

Voltage

Rated operational voltage U _e	240 - 415 V
Continuous operating voltage U _c according to IEC 61643-1	275 V
Voltage protection level U _p according to IEC 61643-1	1,35 kV
Voltage protection level U _p L-PE/N-PE according to IEC 61643-11	1,50 kV
Voltage level U _p L-N/PEN IEC 61643-11	1350 V

Electric current

Nominal discharge current I _n 8 - 20 μs L-N(PEN)/N-PE IEC 61643	20 kA
Max. overcurrent protection device, parallel connection (fuse)	125 A
Max. discharge (I _{max}) L-N(PEN)/ N-PE	40 kA

Dimensions

Height	96,8 mm
Width	35,60 mm
Depth	65,7 mm

Use conditions

Operating temperature	-40 - 80 °C
-----------------------	-------------

Network configuration

Network type	TN-S, TT
--------------	----------

Equipment

With remote signalling contact	Yes
--------------------------------	-----

Connection

Cross-section of input and output with screws, for flexible conductors	1,5 - 25,0 mm ²
Cross-section of input and output with screws, for massive conductors	1,5 - 35,0 mm ²
Cross-section signal contact	0,14 - 1,5 mm ²

Standards

Requirement class IEC 61643	T2
-----------------------------	----

Frequency

Frequency

50 - 60 Hz

Installation, mounting

Nominal tightening torque

3 - 3 Nm