



ST315



Safety transformer 63VA 230V12-24V

Technical properties

Architecture

Fixing mode	DIN rail type O (symmetrical)
-------------	-------------------------------

Configuration

Number of modules	6
-------------------	---

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50 Hz

Voltage

Rated insulation voltage	4000 V
Output voltage 2	24 V
Open circuit voltage secondary	14.2 / 26.5 V
Output voltage	12 / 24 V

Electric current

Output intensity 2	2.63 A
Output intensity	5.25 A

Dimensions

Depth of installed product	68 mm
Height of installed product	85 mm
Width of installed product	105 mm

Power

Power consumed	63 VA
----------------	-------

Installation, mounting

Suitable for surface mounting	Yes
Suitable for flush-mounting	No
Mounting type	din-Rail

Cable

Max. cable length to door actuator release 0.5 A	max. 100 m
Max. cable length to door actuator release 1 A	max. 50 m

Equipment

On/Off switch	No
Short-circuit protected	Yes

Standards

Standard text	EN 61558-2-6
European directive WEEE	concerned

Safety

Protection index IP	IP20
Temperature protection	Yes

Use conditions

Operating temperature	-20...35 °C
-----------------------	-------------
