



TH101



Modular USB interface

Technical properties

Architecture

Fixing mode	Din-Rail
-------------	----------

Configuration

Number of modules	2
-------------------	---

Compatibility

Compatibility	compatible with USB 1.1/2.0 transmission protocols
System requirements:	system requirements: Windows 2000 or later

Connectivity

Connectors / jacks	with B-type USB socket for data traffic (voltage supply via PC)
--------------------	-----------------------------------------------------------------

Voltage

Operating voltage over bus	21...32 V DC
----------------------------	--------------

Dimensions

Width of rail mounted device (RMD)	2 modules
------------------------------------	-----------

Power

Total power loss under IN	0.15 W
Dissipated energy in cable	0.15 W

Storage

Data transmission rate	9.6 kBd
------------------------	---------

Materials

Colour	stone grey
RAL colour	RAL 7035 - Light grey
Material	other

Cable

USB cable length	max. 5 m
------------------	----------

Settings

Supported configuration modes	system
Programming	programmable from ETS3, V1.0

Equipment

Interface type	USB
----------------	-----

Software

Update	with flash-controller technology
application	bus/PC connection
Safety	
Protection index IP	IP20
Use conditions	
Operating temperature	-5...45 °C
Identification	
Main design line	KNX