



SVN121M

Green LED Indicator light 230VAC

Technical properties

Capacity

| | |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

Voltage

| | |
|---|-------------|
| Rated insulation voltage U_i | 250 V |
| Rated impulse withstand voltage U_{imp} | 4000 V |
| Type voltage supply | AC |
| Rated operational voltage U_e | 230 - 230 V |

Use conditions

| | |
|-------------------------------|-------------|
| Operating temperature | -20 - 50 °C |
| Storage/transport temperature | -40 - 80 °C |

Connectivity

| | |
|--------------------|----------------|
| Type of connection | Screw terminal |
|--------------------|----------------|

Connection

| | |
|----------------------------------|---------------------------|
| Cross-section flexible conductor | 0.75 - 6 mm ² |
| Cross-section rigid conductor | 0.75 - 10 mm ² |
| Type of lamp socket | Fix |

Power

| | |
|------------------------------|--------|
| Total power loss under I_N | 0,80 W |
| Power per charging point | 0 |

Dimensions

| | |
|--------|----------|
| Height | 83 mm |
| Width | 17,50 mm |
| Depth | 62 mm |

Lighting

| | |
|--------------|-----|
| Type of lamp | LED |
|--------------|-----|

Materials

| | |
|--------|-------|
| Colour | Green |
|--------|-------|

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|