



TE370

### 3Ph Kwhmeter via CT with KNX output

#### Technical properties

#### Settings

Supported configuration mode ETS

#### Use conditions

Operating temperature -10 - 55 °C

#### Architecture

Bus system KNX

Type of pole 3P+N

#### Connectivity

With bus system Powernet No

Type of connection Direct connection

#### Electric current

Maximum measuring circuit current 5 A