



TRM600AU



Additional Control for latching relay or timer

Technical properties

Architecture

Fixing mode flush-mounting

Functions

Function reset function (to factory setting)

Configuration

Number of modules 0

Controls and indicators

Button / push-button with configuration and function button

Connectivity

Radio protocol KNX Radio

Receiver category 2

Main electrical features

Frequency 50/60 Hz

Electric current

Number of entry circuits 2

Maximum through current 500 mA~

Dimensions

Height of installed product 40 mm

Dimensions (LLxwxh) 40x40x18

Diameter 53 mm

Height 18 mm

Frequency

Transmission frequency 433 MHz

Radio reception frequency 433 MHz

Radio transmission/reception frequency 433.4 MHz

Power

Total power loss under IN 150 mW

Power dissipation per coil 100 mW

Radio transmission power 10 mW

Materials

Colour independent of design lines light grey

LED control

Max number of LED/CFL lamps	0
LED	with configuration and function LEDs

Connection

Conductor cross-section (flexible)	0.5...1.5 mm ²
Conductor cross-section (rigid)	0.5...2.5 mm ²
Type of connection	with screw-in lift terminals
Type of connection	with screw

Settings

Supported configuration modes	PB
Programming	toolless quicklink configuration using buttons and LED display

Scope of delivery

Bus connection included	No
-------------------------	----

Equipment

Number of outputs	1
Number of radio channels	1
Number of quicklink links	max. 20 transmitter/receiver
Modular expandability	No

Safety

REACH conform	No
RoHS conform	Yes
Halogen free	No

Use conditions

Operating temperature	-15...45 °C
Storage/transport temperature	-25...70 °C
Energy-saving	low intrinsic energy requirement
Relative humidity (without condensation)	0...65 % (without condensation)

Identification

Main design line	Electronics platform
------------------	----------------------