



TH101

**Modular USB interface**

**Technical properties**

**Architecture**

Bus system EIB

**Configuration**

Number of modules 2

**Compatibility**

Compatibility compatible with USB 1.1/2.0 transmission protocols

System requirements: system requirements: Windows 2000 or later

**Connectivity**

Connectors / jacks with B-type USB socket for data traffic (voltage supply via PC)

**Voltage**

Operating voltage over bus 21...32 V DC

**Dimensions**

Width of rail mounted device (RMD) 2 modules

**Power**

Total power loss under IN 0.15 W

Dissipated energy in cable 0.15 W

**Storage**

Data transmission rate 9.6 kBd

**Materials**

RAL colour RAL 7035 - Light grey

**Connection**

Connector type USB connector

**Cable**

USB cable length max. 5 m

**Settings**

Supported configuration modes system

Programming programmable from ETS3, V1.0

**Equipment**

Interface type USB

---

**Software**

---

Update	with flash-controller technology
application	bus/PC connection

---

**Use conditions**

---

Operating temperature	-5...45 °C
-----------------------	------------

---

**Identification**

---

Main design line	KNX
------------------	-----

---