



TH101



Modular USB interface

Technical properties

Architecture

Fixing mode Din-Rail

Configuration

Number of modules 2

Compatibility

Compatibility compatible with USB 1.1/2.0 transmission protocols

System requirements: system requirements: Windows 2000 or later

Connectivity

Connectors / jacks with B-type USB socket for data traffic (voltage supply via PC)

Voltage

Operating voltage over bus 21...32 V DC

Dimensions

Width of rail mounted device (RMD) 2 modules

Power

Total power loss under IN 0.15 W

Dissipated energy in cable 0.15 W

Storage

Data transmission rate 9.6 kBd

Materials

Colour stone grey

RAL colour RAL 7035 - Light grey

Material other

Cable

USB cable length max. 5 m

Settings

Supported configuration modes system

Programming programmable from ETS3, V1.0

Equipment

Interface type USB

Software

Update	with flash-controller technology
application	bus/PC connection
Safety	
Protection index IP	IP20
Use conditions	
Operating temperature	-5...45 °C
Identification	
Main design line	KNX