



TJA451

domovea system kit

Technical properties

Architecture

Fixing mode REG

Configuration

Number of modules 10

Controls and indicators

Indicator lamp yes

Remote Control possibility 1

Manual selection switches / push-buttons Selection switch for online/offline mode

Electric current

Current consumption (operation) ≈ 150 mA

Dimensions

Width of rail mounted device (RMD) 10 modules

Storage

Memory allocated to the icons/wallpapers 20 MB

Materials

Colour stone grey

RAL colour RAL 7035 - Light grey

Material other

Material plastic

Type of surface treatment untreated

Connection

Number of IP cameras 10

Bus coupling unit with integral bus coupling unit

Bus connection bus connection via connecting terminal

Type of connection Quickconnect

Settings

Supported configuration modes system

Scope of delivery

Bus connection included Yes

Accessories included

Accessory for Android application Yes

Accessory for IOS application	yes
-------------------------------	-----

Equipment

Number of group	100
Number of controllable outputs	500
Number of clients	30
Number of energie measurement archives	100
Number of sequences	50
Number of USB interfaces	3
With configuration software	Yes

Software

Client software	Yes
-----------------	-----

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	0...45 °C
-----------------------	-----------

Identification

Main design line	KNX
------------------	-----

Instructions

Information text	Network technology skills are required for commissioning. System requirements: Windows XP, VISTA, Windows 7, Windows 8, Windows 10 (32 or 64-bit).
------------------	--