



TXA606D



**Output module 6x 16A (C)/230V~, KNX**

**Technical properties**

**Architecture**

Bus system	yes
Fixing mode	REG

**Functions**

Multi-phase mode	suitable to switch different external conductors
Function	with positioning function for blind and lamella position ; with safety functions e.g. for wind, rain, alarm ; with sun shade function
Switching	For switching, e.g. of 6 independent loads or activation of 3 drives
Operating mode	any combined operation from drive and switching functions possible

**Configuration**

Number of modules	4
-------------------	---

**Controls and indicators**

Indicator lamp	yes
Operation	Manual operation can be activated via selection switch, thereby deactivation of the KNX function
Indication / display	status LED integrated in the manual operation button
Manual selection switches / push-buttons	manual operation buttons for on/off (up/down) and bus function on/off per channel/device
Button / push-button	with illuminated programming button

**Main electrical features**

Rated operational voltage Ue	230 V
Frequency	50/60 Hz
Rated current	16 A

**Voltage**

Operating voltage over bus	21...32 V DC
Output voltage	230 V AC
System supply voltage	30V DC via bus

**Electric current**

Bus current consumption (data transfer)	5 mA
Bus current consumption (idle)	3 mA
Number of entry circuits	0
Maximum through current	16 A
Rated current	16 A

**Dimensions**

Width of rail mounted device (RMD)	4 modules
Height	90 mm

**Power**

Max. power with electronic transfo.	1200 W
Output power	2300 W
Max. switching power	8625 W
Conventional transformers	1600 VA
Electronic transformers	1200 W

**Materials**

Colour	stone grey
--------	------------

**Lighting control**

Fluorescent lamps with electronical ballast (EB)	20 x 36 W
- uncompensated	1200 W

**Fluorescent bulbs control**

Energy-saving lamps	23 W
Power lighting fluo lamps	18x23W
Fluorescent lamps parallel compensated	1500 W /200 µF

**LED control**

Max number of LED/CFL lamps	18
230V LED lamps	18 x 23 W
Power LED	216 W
LED	Status LED integrated in manual operation button

**Incandescent bulbs control**

Max. power with incandescent lamps	2300 W
230 V incandescent lamps and halogen lamps	2300 W

**Connection**

Connection cross-sect. flexible conductor	0,75 / 2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	0,75 / 2.5mm <sup>2</sup>
Type of load	C-Load
Conductor cross-section (flexible)	0.75...2.5 mm <sup>2</sup>
Conductor cross-section (rigid)	0.75...2.5 mm <sup>2</sup>
Type of contacts	6NO
Bus coupling unit	with integral bus coupling unit
Type of connection	with QuickConnect plug-in terminals
Bus connection	bus connection via connecting terminal
Type of connection	quick connect

**Settings**

Supported configuration modes	easy, system
Setting	Switching time on change of direction is preset

**Scope of delivery**

---

Bus connection included	Yes
-------------------------	-----

**Equipment**

---

Number of outputs	6
-------------------	---

---

Modular expandability	No
-----------------------	----

**Use**

---

Differentiation characteristic 3 - Sales	with plug-in terminals
--	------------------------

**Safety**

---

Protection index IP	IP20
---------------------	------

**Use conditions**

---

Operating temperature	-5...45 °C
-----------------------	------------

---

Storage/transport temperature	-20...70 °C
-------------------------------	-------------

**Identification**

---

Device family	TXA
---------------	-----

---

Main design line	KNX
------------------	-----