


TXA608B



easy



quickconnect

## Output module 8x 10A /230V~, KNX

### Technical properties

#### Connectivity

With bus system KNX	Yes
With bus system KNX radio	No

#### Settings

Supported configuration mode	ETS, easy
------------------------------	-----------

#### Dimensions

Number of width units	6
-----------------------	---

#### Materials

Colour	Grey
--------	------

#### Equipment

Radio frequency bidirectional	No
With switch for manual switch	Yes

#### Electric current

Rated current	10 A
Bus current consumption while idle	4 mA

#### Frequency

Frequency	50 - 60 Hz
-----------	------------

#### Power

Output power	1200 W
--------------	--------

#### Voltage

Rated operational voltage Ue	230 - 230 V
System supply voltage	30 V DC Via bus

#### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

#### Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

#### Texts

Function	With safety functions e.g. for wind, rain, alarm, With positioning function for blind and lamella position, With sun shade function
Type of connection	With quickconnect plug-in terminals