


TXA610B



easy

Output module 10x 10A /230V~, KNX

Technical properties

Connectivity

With bus system KNX	Yes
With bus system KNX radio	No

Settings

Supported configuration mode	ETS, easy
------------------------------	-----------

Dimensions

Number of width units	6
-----------------------	---

Materials

Colour	Grey
--------	------

Equipment

Radio frequency bidirectional	No
With switch for manual switch	Yes

Electric current

Rated current	10 A
Bus current consumption while idle	4 mA

Frequency

Frequency	50 - 60 Hz
-----------	------------

Power

Output power	1200 W
--------------	--------

Voltage

Rated operational voltage Ue	230 - 230 V
System supply voltage	30 V DC Via bus

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Texts

Function	With safety functions e.g. for wind, rain, alarm, With positioning function for blind and lamella position, With sun shade function
Type of connection	With quickconnect plug-in terminals