



TJA665

IP20

**easy configuration tool**

**Technical properties**

**Architecture**

Fixing mode REG

**Configuration**

Number of modules 6

**Controls and indicators**

Manual selection switches / push-buttons Selection switch for online/offline mode

Button / push-button with programming button and red programming LED

**Voltage**

Auxiliary voltage 24 V DC

Operating voltage 24 V DC

Operating voltage over bus 21...32 V DC

**Electric current**

Number of entry circuits 512

**Dimensions**

Width of rail mounted device (RMD) 6 modules

**Connection**

Conductor cross-section (flexible) 0.75...2.5 mm<sup>2</sup>

Conductor cross-section (rigid) 0.75...2.5 mm<sup>2</sup>

Bus coupling unit with integral bus coupling unit

Bus connection bus connection via connecting terminal

**Scope of delivery**

Bus connection included Yes

Contents of the kit Configuration tool

**Equipment**

Number of outputs 512

Updateable Yes

Visualization No

Web-Server Yes

**Safety**

Protection index IP IP20

**Use conditions**

Operating temperature	0...45 °C
Storage/transport temperature	-20...70 °C
<b>Identification</b>	
Main design line	KNX
<b>Instructions</b>	
Information text	Network technology skills are required for commissioning. System requirements: Windows 8.1, Android 4.4, iOS 8.