



TXA022



Weekly time switch EASY, 2 modules

Technical properties

Architecture

Bus system	EIB
------------	-----

Functions

Function	Functions e.g. switching, dimming, blinds, light scenes, heating, operating modes, date, time
----------	---

Configuration

Number of modules	2
-------------------	---

Controls and indicators

Indication / display	LCD display for commissioning
Button / push-button	with 5 manual operation buttons

Voltage

Operating voltage over bus	21...32 V DC
System supply voltage	30V DC via bus

Electric current

Bus consumption	4 mA
-----------------	------

Dimensions

Depth of installed product	97 mm
Height of installed product	85 mm
Length	97 mm
Width of installed product	36 mm
Width of rail mounted device (RMD)	2 modules

Power

Total power loss under IN	0.3 W
Dissipated energy in cable	1 W

Battery

Lithium cell power reserve [years]	≈ 5
------------------------------------	-----

Connection

Conductor cross-section (flexible)	1.5...10 mm ²
Conductor cross-section (rigid)	1...6 mm ²
Bus coupling unit	with integral bus coupling unit
Bus connection	bus connection via connecting terminal

Settings

Number of program steps	56
Supported configuration modes	system, easy
Summer / Winter time change	automatic
Shortest switching time	1 mn
Type of programming	digital
Astro program	No

Scope of delivery

Bus connection included	Yes
-------------------------	-----

Equipment

Number of outputs	2
Number of channels	2
Supply failure reserve	lithium battery
With holidays program	Yes
With random program	Yes

Use

Cycle	weekly
Differentiation characteristic 1 - Sales	with hinged cover
Differentiation characteristic 2 - Sales	with display
Differentiation characteristic 3 - Sales	with integrated bus coupling unit

Safety

Protection index IP	IP20
REACH conform	No
Key	with programming key

Use conditions

Operating temperature	0...45 °C
Storage/transport temperature	-20...70 °C

Identification

Main design line	KNX
------------------	-----