



TXA628C

## OUTPUT DEVICE FOR 8 SHUTTERS / BLINDS 230V~ 6A / NE

### Technical properties

#### Architecture

Bus system	KNX
Number of blinds/shutters outputs	8
Fixing mode	REG

#### Functions

Bus module detachable	No
Multi-phase mode	suitable to switch different external conductors

#### Configuration

Number of modules	6
-------------------	---

#### Controls and indicators

Indicator lamp	yes
Manual selection switches / push-buttons	8 manual operation buttons for up/down per channel/device

#### Main electrical features

Type of supply voltage	AC
Frequency	50/60 Hz
Rated current	6 A

#### Voltage

Auxiliary voltage	230...240 V AC
Operating voltage over bus	21...32 V DC
System supply voltage	30V DC via bus

#### Electric current

Bus current consumption (data transfer)	6 mA
Bus current consumption (idle)	4 mA
Number of entry circuits	0
Maximum switching current	6 A
Switching current at $\cos \varphi = 0.6$	max. 6 A

#### Dimensions

Width of rail mounted device (RMD)	6 modules
Height	90 mm

#### Power

Contact rating with 230 V in AC1	1200 W
----------------------------------	--------

**Materials**

Colour	light grey
--------	------------

**Connection**

Conductor cross-section (flexible)	0.75...2.5 mm <sup>2</sup>
------------------------------------	----------------------------

Conductor cross-section (rigid)	0.75...2.5 mm <sup>2</sup>
---------------------------------	----------------------------

Number of contacts	8
--------------------	---

Bus coupling unit	with integral bus coupling unit
-------------------	---------------------------------

Bus connection	bus connection via connecting terminal
----------------	--

**Settings**

Supported configuration modes	system
-------------------------------	--------

**Scope of delivery**

Bus connection included	Yes
-------------------------	-----

**Equipment**

Modular expandability	No
-----------------------	----

**Safety**

Protection index IP	IP20
---------------------	------

**Use conditions**

Operating temperature	-5...45 °C
-----------------------	------------

Storage/transport temperature	-20...70 °C
-------------------------------	-------------

**Identification**

Main design line	KNX
------------------	-----