



TXM632C



OUTPUT DEVICE FOR 12 SHUTTERS / BLINDS 230V~ 4A / NE

Technical properties

Architecture

Bus system	KNX
Number of blinds/shutters outputs	12
Fixing mode	REG

Functions

Bus module detachable	No
Multi-phase mode	suitable to switch different external conductors

Configuration

Number of modules	10
-------------------	----

Controls and indicators

Indicator lamp	yes
Manual selection switches / push-buttons	6 manual operation buttons for up/down per channel/device

Main electrical features

Type of supply voltage	AC
Frequency	50/60 Hz
Rated current	4 A

Voltage

Auxiliary voltage	230...240 V AC
Operating voltage over bus	21...32 V DC
System supply voltage	30V DC via bus

Electric current

Bus current consumption (data transfer)	7 mA
Bus current consumption (idle)	5 mA
Number of entry circuits	0
Maximum switching current	4 A
Switching current at $\cos \phi = 0.6$	max. 4 A

Dimensions

Width of rail mounted device (RMD)	10 modules
Height	90 mm

Power

Contact rating with 230 V in AC1	920 W
----------------------------------	-------

Materials	
Colour	light grey
Connection	
Conductor cross-section (flexible)	0.75...2.5 mm ²
Conductor cross-section (rigid)	0.75...2.5 mm ²
Bus coupling unit	with integral bus coupling unit
Type of connection	with screw terminals
Bus connection	bus connection via connecting terminal
Settings	
Supported configuration modes	system
Scope of delivery	
Bus connection included	Yes
Equipment	
Modular expandability	No
Safety	
Protection index IP	IP20
REACH conform	No
RoHS conform	Yes
Halogen free	No
Use conditions	
Operating temperature	-5...45 °C
Storage/transport temperature	-20...70 °C
Identification	
Main design line	KNX