




TYA604C



Output module 4x 16A /230V~, KNX

Technical properties

Connectivity

With bus system KNX	Yes
With bus system KNX radio	No

Settings

Supported configuration mode	ETS
------------------------------	-----

Dimensions

Depth	65 mm
Number of width units	4

Materials

Colour	Light grey
--------	------------

Equipment

Radio frequency bidirectional	No
With switch for manual switch	Yes

Electric current

Rated current	16 A
Bus current consumption while idle	3 mA

Frequency

Frequency	50 - 60 Hz
-----------	------------

Power

Power incandescent lamp 230 V	2300 - 2300 W
Output power	2300 W

Voltage

Rated operational voltage U _e	230 - 230 V
System supply voltage	30 V DC Via bus

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Texts

Function	With safety functions e.g. for wind, rain, alarm, With positioning function for blind and lamella position, With sun shade function
----------	---

