



TXA624C



OUTPUT DEVICE FOR 4 SHUTTERS / BLINDS 230V~ 6A / NE

Technical properties

Architecture

Bus system	KNX
Number of blinds/shutters outputs	4
Fixing mode	REG

Functions

Bus module detachable	No
Multi-phase mode	suitable to switch different external conductors

Configuration

Number of modules	4
-------------------	---

Controls and indicators

Indicator lamp	yes
Manual selection switches / push-buttons	4 manual operation buttons for up/down per channel/device

Main electrical features

Type of supply voltage	AC
Frequency	50/60 Hz
Rated current	6 A

Voltage

Operating voltage over bus	21...32 V DC
System supply voltage	30V DC via bus

Electric current

Bus current consumption (data transfer)	5 mA
Bus current consumption (idle)	3 mA
Number of entry circuits	0
Maximum switching current	6 A
Switching current at $\cos \varphi = 0.6$	max. 6 A

Dimensions

Width of rail mounted device (RMD)	4 modules
Height	90 mm

Power

Contact rating with 230 V in AC1	1200 W
----------------------------------	--------

Materials

Colour light grey

Connection

Conductor cross-section (flexible)	0.75...2.5 mm ²
Conductor cross-section (rigid)	0.75...2.5 mm ²
Number of contacts	4
Bus coupling unit	with integral bus coupling unit
Bus connection	bus connection via connecting terminal

Settings

Supported configuration modes system

Scope of delivery

Bus connection included Yes

Equipment

Modular expandability No

Safety

Protection index IP IP20

Use conditions

Operating temperature -5...45 °C

Storage/transport temperature -20...70 °C

Identification

Main design line KNX