


TYA624B



Shutter module 4x 6A /24V DC, KNX

Technical properties

Settings

Supported configuration mode ETS

Connectivity

With bus system KNX radio No

Installation, mounting

Mounting on DIN rail

Equipment

With switch for manual switch Yes

Materials

Colour Light grey

Electric current

Rated current 6 A

Max. switching current 6 A

Voltage

Operating voltage over bus 21 - 32 V

Use conditions

Operating temperature -5 - 45 °C

Connection

Cross-section flexible conductor 0.75 - 2.5 mm²

Cross-section rigid conductor 0.75 - 2.5 mm²

Capacity

Number of modules 4

Texts

Function With positioning function for roller shutter position, With safety functions e.g. for wind, rain, alarm, With sun shade function

Type of connection With quickconnect plug-in terminals