



VD108TT

Sm.distr.,VD/IC²,surface,1row,8M,IP40,MS-terminals,N+PE,AUS,transparent door

Technical properties

Architecture

Fixing mode	surface-mounting
-------------	------------------

Functions

With a pipe-in lead	Yes
---------------------	-----

Configuration

Number of modules	8
-------------------	---

Main electrical features

Nominal voltage	400 V
-----------------	-------

Electric current

Rated current	63 A
---------------	------

Dimensions

Depth of installed product	91 mm
Internal depth	72 mm
Height of installed product	170 mm
Width of installed product	170.5 mm

Cover, door

Identification of protection index	40
Interlockable	No
Number of keylock of the door	0
Cover type	Closed (plain)
Door locking	without
Door leave	single
Cover type	Door
Transparent cover or door	Yes

Materials

Colour	pure white
Colour	white
RAL colour	RAL 9010 - Pure white
Material	plastic
Type of surface treatment	untreated

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Settings

Enclosure type

Distributor empty cabinet

Equipment

Number of rows

1

Quantity of section in width

1

Quantity of rails

1

Can be accessorized

Yes

Number of openings for flange plates

0

Extension possible

No

Earthing terminal block

Yes

Neutral terminal block

Yes

Signal passing door

Yes

Standards

GWT Glow wire test

650 °C

European directive WEEE

not concerned

Safety

Protection index IP

IP40

Protection class

isol.class II

REACH conform

No

RoHS conform

Yes

Halogen free

Yes

Use conditions

Operating temperature

-25...40 °C