



VD118PT

Sm.distr.,VD/IC<sup>2</sup>,surface,1row,18M,IP40,MS-terminals,AUS,N+PE,white door

### Technical properties

#### Voltage

|                 |             |
|-----------------|-------------|
| Nominal voltage | 400 - 400 V |
|-----------------|-------------|

#### Installation, mounting

|                            |                  |
|----------------------------|------------------|
| Suitable for outdoor usage | No               |
| Mounting on                | Surface mounting |

#### Electric current

|               |      |
|---------------|------|
| Rated current | 63 A |
|---------------|------|

#### Equipment

|                             |     |
|-----------------------------|-----|
| Number of rails             | 1   |
| Number of rows              | 1   |
| Number of section in width  | 1   |
| With lock                   | No  |
| Has neutral terminal block  | Yes |
| Has earthing terminal block | Yes |
| Has mounting plate          | No  |

#### Capacity

|                   |    |
|-------------------|----|
| Number of modules | 18 |
|-------------------|----|

#### Functions

|                     |     |
|---------------------|-----|
| With conduit inlets | Yes |
|---------------------|-----|

#### Dimensions

|                       |        |
|-----------------------|--------|
| Height                | 200 mm |
| Width                 | 400 mm |
| Depth                 | 91 mm  |
| Number of width units | 18     |

#### Cover, door

|                           |    |
|---------------------------|----|
| Number of cabinet doors   | 1  |
| Number of locks           | 0  |
| Door/cover is transparent | No |

#### Materials

|                       |            |
|-----------------------|------------|
| Material              | Plastic    |
| RAL code              | 9010       |
| Colour                | Pure white |
| Ultraviolet-resistant | No         |

**Safety**

---

|                               |                            |
|-------------------------------|----------------------------|
| Protection class              | Isolation class II         |
| Ingress Protection (IP) class | IP40                       |
| Locking type                  | Snap on lock, Without lock |
| Glow wire test                | 650 °C                     |

---