



TYA661BN



**Dimmer 1 channel 600W**

**Technical properties**

**Functions**

Bus module detachable	No
Multi-phase mode	suitable to switch different external conductors
Function	Learning function for optimised operation of compact fluorescent lamps and LED luminaires can be activated via the bus
Soft startup	bulb-preserving soft startup

**Configuration**

Number of modules	4
-------------------	---

**Controls and indicators**

With LED indication	Yes
Indicator lamp	yes
Operation	manual operation also possible without bus, e.g. on building site ; Manual operation can be activated via selection switch, thereby deactivation of the KNX function ; Manual operation per channel via button with integrated status LED, thereby lockout of KNX function
Indication / display	status LED integrated in the manual operation button
Manual selection switches / push-buttons	selection switch for manual/bus operation as well as load setting
Button / push-button	with illuminated programming button

**Main electrical features**

Frequency	50/60 Hz
Rated current	2.3 A

**Voltage**

Auxiliary voltage	230 V AC
Input voltage	230 V AC
Operating voltage over bus	21...32 V DC

**Electric current**

Bus current consumption (data transfer)	< 2.3 mA
---	----------

**Fuse**

Fuse	short-circuit proof and overload proof (display using LEDs) ; overheating protection (display using LEDs)
------	---

**Dimensions**

Width of rail mounted device (RMD)	4 modules
------------------------------------	-----------

<b>Power</b>	
Dimmable conventional transformers	600 VA
Incandescent bulb power	600 W
Total power loss under IN	320 mW
Power dissipation per coil	180 mW
Electronic transformers	600 W

### Power supply

Supply voltage	230 V AC
----------------	----------

### Fluorescent bulbs control

Dimmable energy-saving lamps	120 W
Power lighting fluo lamps	120W

### LED control

Max number of LED/CFL lamps	10
Dimmable LED lamps	120 W
Dimmable 230 V retrofit LED lamps	per channel 120 W
Power LED	120 W

LED	Status LED integrated in manual operation button ; Overheating protection, display using LEDs ; Overload protection, display via LED
-----	--

### Incandescent bulbs control

230 V incandescent lamps and halogen lamps	600 W
--	-------

### Connection

Connection cross-sect. flexible conductor	0,75 / 2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	0,75 / 2.5mm <sup>2</sup>
Type of load	universal
Conductor cross-section (flexible)	0.75...2.5 mm <sup>2</sup>
Conductor cross-section (rigid)	0.75...2.5 mm <sup>2</sup>
Bus coupling unit	with integral bus coupling unit
Type of connection	with QuickConnect plug-in terminals
Bus connection	bus connection via connecting terminal
Type of connection	quick connect

### Settings

Supported configuration modes	system
Parameterisation	parameter definable behaviour in the event of bus voltage failure/return

### Scope of delivery

Bus connection included	Yes
-------------------------	-----

### Equipment

Type of dimmer	dimming actuator
Modular expandability	No
Dimming principle	phase cut-on or cut-off according to load type, self-learning ; minimum/maximum dimming values per channel settable on device

low noise

very low noise

---

**Use**

Local operation/hand operation Yes

---

**Safety**

REACH conform No

RoHS conform Yes

Halogen free No

Protection with overheating, overload and short-circuit protection

---

**Use conditions**

Operating temperature -5...45 °C

Storage/transport temperature -20...70 °C

---

**Identification**

Main design line KNX