



VF108PT

Small distributor,golf,flush,1row,8M,IP40,MS-terminal,Australia,N+PE,white door

Technical properties

Architecture

Fixing mode flush-mounting

Functions

With a pipe-in lead Yes

Configuration

Number of modules 8

Main electrical features

Nominal voltage 400 V

Electric current

Rated current 80 A

Dimensions

Insertion depth 72 mm

Depth of wall niche 72 mm

Depth of installed product 97.5 mm

Internal depth 97.5 mm

Height of installed product 225 mm

Installation height 189 mm

Width of installed product 275 mm

Width in division units 8

Built-in height 189 mm

Built-in width 242 mm

Cover, door

Type of door closing Latch

Identification of protection index 40

Interlockable No

Number of keylock of the door 0

Cover type Closed (plain)

Door locking without

Door leave single

Cover type Door

Transparent cover or door No

Materials

Colour pure white

Colour	white
RAL colour	RAL 9010 - Pure white
Material	plastic
Type of surface treatment	untreated
Installation, mounting	
Suitable for outdoor use	No
Settings	
Enclosure type	Distributor empty cabinet
Equipment	
Number of rows	1
Quantity of section in width	1
Quantity of rails	1
Can be accessorized	Yes
Number of openings for flange plates	0
Extension possible	Yes
Earthing terminal block	Yes
Neutral terminal block	Yes
Signal passing door	Yes
Standards	
GWT Glow wire test	850 °C
European directive WEEE	concerned
Safety	
IK protection code against mechanical impacts	07
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes
Halogen free	No
Impact strength	IK07
Use conditions	
Operating temperature	-25...40 °C