



TYB692F



Output module 2x 6A /230V~, 2 inputs, flush mounted, KNX

Technical properties

Architecture

Fixing mode	flush-mounting
-------------	----------------

Configuration

Number of modules	0
-------------------	---

Controls and indicators

Indicator lamp	yes
----------------	-----

Main electrical features

Rated operational voltage Ue	230 V
Rated current	6 A

Voltage

Max. switching capacity at	230 V AC
Operating voltage over bus	21...32 V DC
System supply voltage	30V DC via bus

Electric current

Bus current consumption (data transfer)	7 mA
Bus current consumption (idle)	5 mA
Number of entry circuits	2
Maximum through current	6 A
Rated current	6 A
Switching current at $\cos \varphi = 0.8$	max. 6 A
Withstand current in AC1 for the contact path or zone 1	6 A

Dimensions

Height of installed product	44 mm
Dimensions (LLxwwxhh)	44 x 43 x 22 mm
Width of rail mounted device (RMD)	0 modules
Height	44 mm

Power

Max. power with electronic transfo.	500 W
Total power loss under IN	0.5 W
Output power	500 W
Max. switching power	1200 W
Conventional transformers	500 VA
Electronic transformers	500 W

Measurement

Input scanning voltage	12 V DC V DC
------------------------	--------------

Materials

Colour	light grey
--------	------------

Lighting control

Fluorescent lamps with electronical ballast (EB)	6 x 48 W
- uncompensated	500 VA

Fluorescent bulbs control

Power lighting fluo lamps	5 x 13W
Max. power fluo. duo lamp comp. series	6 x 48W

LED control

Max number of LED/CFL lamps	5
Power LED	65 W

Incandescent bulbs control

Max. power with incandescent lamps	500 W
230 V incandescent lamps and halogen lamps	500 W

Connection

Conductor cross-section (flexible)	0.75...2.5 mm ²
Conductor cross-section (rigid)	0.75...2.5 mm ²
Number of contacts	2
Type of contacts	1NO
Bus coupling unit	with integral bus coupling unit
Type of connection	with screw terminals

Settings

Supported configuration modes	system
-------------------------------	--------

Scope of delivery

Bus connection included	Yes
-------------------------	-----

Equipment

Modular expandability	No
-----------------------	----

Use

Differentiation characteristic 3 - Sales	with screw terminals
--	----------------------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-5...45 °C
Storage/transport temperature	-20...70 °C

Identification

Subject to technical modifications

