



VF218PT

Small distributor,golf,flush,2row,36M,IP40,MS-terminal,Australia,N+PE,white door

Technical properties

Voltage

Nominal voltage	400 - 400 V
-----------------	-------------

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Flush mounting

Electric current

Rated current	80 A
---------------	------

Equipment

Number of rails	2
Number of rows	2
Number of section in width	1
With lock	No
Has neutral terminal block	Yes
Has earthing terminal block	Yes
Has mounting plate	No

Capacity

Number of modules	36
-------------------	----

Functions

With conduit inlets	Yes
---------------------	-----

Dimensions

Height	418 mm
Width	460 mm
Depth	97,50 mm
Built-in height	382 mm
Built-in width	426 mm
Built-in depth	72 mm
Number of width units	18

Cover, door

Number of cabinet doors	1
Number of locks	0
Door/cover is transparent	No

Materials

Material	Plastic
----------	---------

RAL code	9010
Colour	Pure white
Ultraviolet-resistant	No

Safety

Protection class	Isolation class II
Impact resistance IK	IK07
Ingress Protection (IP) class	IP40
Locking type	Snap on lock, Without lock
Glow wire test	850 °C