



VF212PT

Small distributor,golf,flush,2row,24M,IP40,MS-terminal,Australia,N+PE,white door

Technical properties

Voltage

Nominal voltage 400 - 400 V

Installation, mounting

Suitable for outdoor usage No

Mounting on Flush mounting

Electric current

Rated current 80 A

Equipment

Number of rails 2

Number of rows 2

Number of section in width 1

With lock No

Has neutral terminal block Yes

Has earthing terminal block Yes

Has mounting plate No

Capacity

Number of modules 24

Functions

With conduit inlets Yes

Dimensions

Height 418 mm

Width 382 mm

Depth 97,50 mm

Built-in height 382 mm

Built-in width 318 mm

Built-in depth 72 mm

Number of width units 12

Cover, door

Number of cabinet doors 1

Number of locks 0

Door/cover is transparent No

Materials

Material Plastic

RAL code	9010
Colour	Pure white
Ultraviolet-resistant	No

Safety

Protection class	Isolation class II
Impact resistance IK	IK07
Ingress Protection (IP) class	IP40
Locking type	Snap on lock, Without lock
Glow wire test	850 °C